

Eaton HGLL 8

Catalog Number: HGLL 8

Eaton Crouse-Hinds series HGLL grounding bushing, Rigid/IMC, Aluminum lug, #1/0-8 AWG, Malleable iron, 150°C, Threaded, 3"

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series HGLL grounding bushing	HGLL 8
	UPC
	784564113177
Product Length/Depth	Product Height
4 in	1 in
Product Width	Product Weight
4 in	0.69 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Conduit type

Rigid/IMC

Temperature rating

150°C

Lug material

Aluminum

Thread

Threaded

Trade size

3"

Lug size

#1/0-8 AWG

Material

Malleable iron

Resources

Catalogs

[Crouse-Hinds series Grounding Bushings - Rigid-IMC catalog page](#)

Certification reports

[Grounding Bushings - Rigid-IMC UL certification](#)

[Grounding Bushings - Rigid-IMC Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - HGLL 8](#)