

Eaton HLQ-3-2{10-T

Catalog Number: HLQ-3-2/10-T

Eaton Bussmann series, in-line fuseholder, 300v, 1-10 A, 10 kaic, #18 awg red insulated solid copper wire attached to lineside, used with glq fuses, non indicating, single-pole

General specifications



Catalog Number

HLQ-3-2/10-T

Product Length/Depth

2.25 in

Product Width

0.85 in

Warranty

Not Applicable

UPC

051712154581

Product Height

0.85 in

Product Weight

0.055 lb

Compliances

Contact factory

Photo is representative

Type

In-Line fuseholder

Amperage Rating

1-10A

Number of Poles

Single-pole

Used with

Used with GLQ fuses

Interrupt rating

10 kAIC

Fuse indicator

Non-indicating

Connection

#18 AWG red insulated solid copper wire attached to lineside

Voltage rating

300 V

Catalogs

HLQ-3-2/10-T-HLQ-3-2-10-T-FUSE HOLDER W/ GMQ-3-2/10

Bussmann series complete full line catalog no. 1007

Specifications and datasheets

Eaton Specification Sheet - HLQ-3-2/10-T



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia