

# Eaton HT20P11F2516LS40

Catalog Number: HT20P11F2516LS40

Eaton K-Factor nonlinear ventilated transformer, KT-4 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 115°C rise, 25 kVA, 16, LS, 40



Photo is representative

## General specifications

|  |                       |
|--|-----------------------|
| <b>Product Name</b>  | <b>Catalog Number</b> |
| Eaton K-Factor nonlinear ventilated transformer  | HT20P11F2516LS40      |
|  | <b>UPC</b>            |
|  | 786680207693          |
| <b>Product Length/Depth</b>  | <b>Product Height</b> |
| 20.36 in   | 37.59 in              |
| <b>Product Width</b>   | <b>Product Weight</b> |
| 22.87 in   | 373 lb                |
| <b>Warranty</b>  | <b>Compliances</b>    |
| Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |                       |
|  | <b>Certifications</b> |
|  | UL Listed             |
|  | <b>Catalog Notes</b>  |
|  | DOE 2016 Efficient    |

## Physical Attributes

### Coil material

Aluminum

### Wiring connection

261A

### Type

K-Factor ventilated transformer

### Frame

818

### Tap size

2 at +2.5% FCAN 4 at -2.5% FCBN

## Performance Ratings

### Frequency rating

60 Hz

### Volt ampere rating

25 kVA

### Phase

Single-phase

### Primary voltage

240 x 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

## Miscellaneous

### Special features

Electrostatically shielded

### Weathershield

WS11

## Resources

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - HT20P11F2516LS40](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)