

# Eaton HT29M11S2516CU

Catalog Number: HT29M11S2516CU

Eaton K-Factor nonlinear ventilated transformer, KT-4 (1-phase), PV 208V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise, 25 kVA, 16, Copper windings



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton K-Factor nonlinear ventilated transformer	HT29M11S2516CU
	<b>UPC</b>
	786680207174
<b>Product Length/Depth</b>	<b>Product Height</b>
20.36 in	37.59 in
<b>Product Width</b>	<b>Product Weight</b>
22.87 in	437 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Catalog Notes</b>
	DOE 2016 Efficient

## Physical Attributes

### Coil material

Copper

### Enclosure

NEMA 2

### Wiring connection

264A

### Type

Nonlinear, ventilated transformer

### Frame

818

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

## Performance Ratings

### Frequency rating

60 Hz

### Volt ampere rating

25 kVA

### Phase

Single-phase

### Primary voltage

208 V

### Secondary Voltage

120/240 V

### Temperature rise

150 °C rise

## Miscellaneous

### Special features

Electrostatically shielded

### Weathershield

WS11

## Resources

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - HT29M11S2516CU](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)