

Eaton HT29M11S5016

Catalog Number: HT29M11S5016

Eaton K-Factor nonlinear ventilated transformer, KT-4 (1-phase), PV 208V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise, 50 kVA, 16



Photo is representative

General specifications

Product Name	Catalog Number
Eaton K-Factor nonlinear ventilated transformer	HT29M11S5016
	UPC
	786680207556
Product Length/Depth	Product Height
23.84 in	42.03 in
Product Width	Product Weight
24.22 in	686 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	DOE 2016 Efficient

Physical Attributes

Coil material

Aluminum

Frame

820

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Performance Ratings

Frequency rating

60 Hz

Volt ampere rating

50 kVA

Phase

Single-phase

Primary voltage

208 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Miscellaneous

Special features

Electrostatically shielded

Weathershield

WS16

Resources

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - HT29M11S5016](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)