

Eaton HT8CBRAB-POP

Catalog Number: HT8CBRAB-POP

30.5 mm, Watertight/Oiltight-HT800, Pushbutton, 40 mm, NEMA 1, 2, 3, 3R, 4, 4X, 12, Non-illuminated, Two-position, Maintained push, maintained pull, Red actuator, Round head mushroom head, Plastic, NO, NC, Chrome bezel

General specifications



Photo is representative

Product Name

Eaton HT800 pushbutton

UPC

786685284941

Product Height

3 in

Product Weight

0.5 lb

Certifications

CSA Certified

UL Listed

Catalog Number

HT8CBRAB-POP

Product Length/Depth

7 in

Product Width

6 in

Warranty

1 year

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Actuator color

Red

Bezel

Chrome

Bus material

Plastic

Product Category

Pushbutton

Enclosure

NEMA 4X

NEMA 1

NEMA 3

NEMA 3R

NEMA 2

NEMA 12

NEMA 4

Actuator

Round head mushroom head

Illumination

Non-illuminated

Number of positions

2

Operating mode

Push: maintained, pull: maintained

Size

40 mm

Contact configuration

NO, NC

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - HT8CBRAB-POP](#)

[Quick Selector - HT800 Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)