

# Eaton HT8CFL

Catalog Number: HT8CFL

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight-HT800, Pushbutton, 40 mm, NEMA 1, 2, 3, 3R, 4, 4X, 12, Non-illuminated, Three-position, Maintained push, momentary pull, Gray actuator, Mushroom , Plastic, Chrome bezel

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton HT800 pushbutton	HT8CFL
<b>UPC</b>	<b>Product Length/Depth</b>
782113682433	2.094 in
<b>Product Height</b>	<b>Product Width</b>
5.051 in	2.375 in
<b>Product Weight</b>	<b>Warranty</b>
1 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed CSA Certified

## defaultTaxonomyAttributeLabel

### Type

Push-Pull

### Actuator color

Gray

### Bezel

Chrome

### Bus material

Anodized aluminum

### Enclosure

NEMA 4

NEMA 2

NEMA 4X

NEMA 12

NEMA 1

NEMA 3

NEMA 3R

### Actuator material

Plastic

### Actuator

Mushroom

### Operating mode

Push: maintained

Pull: momentary

### Illumination

Non-illuminated

### Series

HT800

### Number of positions

3

### Degree of protection

NEMA 3R

NEMA 12

NEMA 4

NEMA 4X

NEMA 13

NEMA 3

### Product category

## Resources

### Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Quick Selector - HT800 Pilot Devices](#)

[Eaton Specification Sheet - HT8CFL](#)

Pushbutton

Size

40 mm



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)