

Eaton HT8DBH

Catalog Number: HT8DBH

Eaton HT800 pushbutton, Pushbutton, 40 mm, NEMA 1, 2, 3, 3R, 4, 4X, 12, Non-illuminated, Two-position, Maintained push, Maintained pull, Flat mushroom , Plastic, Chrome bezel, 30.5 mm, Watertight/Oiltight-HT800

General specifications



Product Name	Catalog Number
Eaton HT800 pushbutton	HT8DBH
UPC	Product Length/Depth
782116334346	2.4 in
Product Height	Product Width
3.2 in	2.1 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified

defaultTaxonomyAttributeLabel

Type

Push-Pull

Actuator color

Black

Bezel

Chrome

Bus material

Anodized aluminum

Enclosure

NEMA 1

NEMA 4X

NEMA 2

NEMA 3R

NEMA 4

NEMA 12

NEMA 3

Actuator material

Plastic

Actuator

Flat mushroom

Operating mode

Maintained

Illumination

Non-illuminated

Series

HT800

Number of positions

2

Degree of protection

NEMA 3R

NEMA 4

NEMA 4X

NEMA 13

NEMA 12

NEMA 3

Product category

Pushbutton

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - HT8DBH](#)

[Quick Selector - HT800 Pilot Devices](#)

Size

40 mm



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)