

# Eaton HT8DBRB

Catalog Number: HT8DBRB

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight-HT800, Pushbutton, NEMA 1, 2, 3, 3R, 4, 4X, 12, Non-illuminated, Two position, Maintained push, maintained pull, Flat head mushroom head, Plastic, Chrome bezel



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton HT800 pushbutton	HT8DBRB
<b>UPC</b>	<b>Product Length/Depth</b>
782116334384	6.45 in
<b>Product Height</b>	<b>Product Width</b>
1.4 in	2 in
<b>Product Weight</b>	<b>Warranty</b>
0.4 lb	1 year
<b>Certifications</b>	
UL Listed	
CSA Certified	

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Watertight/Oiltight-HT800

### Bezel

Chrome

### Bus material

Plastic

### Enclosure

NEMA 1

NEMA 3R

NEMA 4X

NEMA 3

NEMA 4

NEMA 12

NEMA 2

### Actuator

Flat head mushroom head

### Operating mode

Pull: maintained

Push: maintained

### Illumination

Non-illuminated

### Number of positions

2

### Product category

Pushbutton

### Size

40 mm

## Resources

### Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - HT8DBRB](#)

[Quick Selector - HT800 Pilot Devices](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)