

Eaton HT8FBGABF7

Catalog Number: HT8FBGABF7

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units, Standard Actuator, Green, 1NO-1NC, Illuminated, Green, LED, full voltage, 120 Vac/Vdc Light Unit, Two-position, Maintained push, maintained pull, HT800 Series



Photo is representative

General specifications

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8FBGABF7
UPC	Product Length/Depth
782116303526	2.094 in
Product Height	Product Width
5.051 in	2.375 in
Product Weight	Warranty
1 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

Catalog Notes

Complete illuminated push-pull switches will not fit in a standard 3 in deep enclosure.

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Enclosure

NEMA 12
NEMA 3
NEMA 4X
NEMA 3R
NEMA 4

Operating mode

Push: maintained
Pull: maintained

Contact configuration

1 NO-1 NC

Illumination

Illuminated

Series

HT800

Light unit type

LED, full voltage

Light unit voltage

120 Vac/dc

Lens color

Green

Number of positions

2

Rating

NEMA 13
NEMA 4X
NEMA 3
NEMA 12
NEMA 4
NEMA 3R

Product category

Illuminated push-pull units

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Quick Selector - HT800 Pilot Devices

Eaton Specification Sheet - HT8FBGABF7



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)