

# Eaton HT8FBGBF7

Catalog Number: HT8FBGBF7

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units, Standard Actuator, Green, 1NC, Illuminated, Green, LED, full voltage, 120 Vac/Vdc Light Unit, Two-position, Maintained push, maintained pull, HT800 Series



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton HT800 pushbutton	HT8FBGBF7
<b>UPC</b>	<b>Product Length/Depth</b>
782116303502	2.094 in
<b>Product Height</b>	<b>Product Width</b>
5.051 in	2.375 in
<b>Product Weight</b>	<b>Warranty</b>
1 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed CSA Certified

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Watertight/Oiltight-HT800

### Enclosure

NEMA 3R  
NEMA 4X  
NEMA 4  
NEMA 12  
NEMA 3

### Operating mode

Push: maintained  
Pull: maintained

### Contact configuration

1 NC

### Illumination

Illuminated

### Series

HT800

### Light unit type

LED, full voltage

### Light unit voltage

120 Vac/dc

### Lens color

Green

### Number of positions

2

### Rating

NEMA 12  
NEMA 4X  
NEMA 3  
NEMA 13  
NEMA 4  
NEMA 3R

### Product category

Illuminated push-pull units

## Resources

### Brochures

Pushbuttons and Indicating Lights  
HT800 30.5 mm pilot devices

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Quick Selector - HT800 Pilot Devices  
Eaton Specification Sheet - HT8FBGBF7



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)