

Eaton HT8FBGBV3

Catalog Number: HT8FBGBV3

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units, Standard Actuator, Green, 1NC, Illuminated, Green, Incandescent, full voltage, 24 Vac/Vdc Light Unit, Two-position, Maintained push, maintained pull, HT800 Series

General specifications



Photo is representative

Product Name
Eaton HT800 pushbutton

UPC
782116303267

Product Height
5.051 in

Product Weight
1 lb

Compliances
CE Marked

Catalog Number
HT8FBGBV3

Product Length/Depth
2.094 in

Product Width
2.375 in

Warranty
1 year

Certifications
CSA Certified
UL Listed

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Enclosure

NEMA 4
NEMA 4X
NEMA 3
NEMA 3R
NEMA 12

Operating mode

Push: maintained
Pull: maintained

Contact configuration

1 NC

Illumination

Illuminated

Series

HT800

Light unit type

Incandescent, full voltage

Light unit voltage

24 Vac/dc

Lens color

Green

Number of positions

2

Rating

NEMA 4
NEMA 12
NEMA 4X
NEMA 3R
NEMA 3
NEMA 13

Product category

Illuminated push-pull units

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - HT8FBGBV3](#)

[Quick Selector - HT800 Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)