

# Eaton HT8FBGBV7

Catalog Number: HT8FBGBV7

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units, Standard Actuator, Green, 1NC, Illuminated, Green, Incandescent, full voltage, 120 Vac/Vdc Light Unit, Two-position, Maintained push, maintained pull, HT800 Series

## General specifications



Photo is representative

**Product Name**  
Eaton HT800 pushbutton

**UPC**  
782116303342

**Product Height**  
5.051 in

**Product Weight**  
1 lb

**Compliances**  
CE Marked

**Catalog Number**  
HT8FBGBV7

**Product Length/Depth**  
2.094 in

**Product Width**  
2.375 in

**Warranty**  
1 year

**Certifications**  
UL Listed  
CSA Certified

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Watertight/Oiltight-HT800

### Enclosure

NEMA 4  
NEMA 4X  
NEMA 12  
NEMA 3R  
NEMA 3

### Operating mode

Push: maintained  
Pull: maintained

### Contact configuration

1 NC

### Illumination

Illuminated

### Series

HT800

### Light unit type

Incandescent, full voltage

### Light unit voltage

120 Vac/dc

### Lens color

Green

### Number of positions

2

### Rating

NEMA 12  
NEMA 4  
NEMA 3  
NEMA 4X  
NEMA 13  
NEMA 3R

### Product category

Illuminated push-pull units

## Resources

### Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Quick Selector - HT800 Pilot Devices](#)

[Eaton Specification Sheet - HT8FBGBV7](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)