

Eaton HT8FBRABFL7P

Catalog Number: HT8FBRABFL7P

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units,low profile light units,Standard Actuator,Red,1NO-1NC,Illuminated,Red,LED, full voltage,120 Vac/Vdc Light Unit,Two-position,Maintained push, maintained pull,Fingerproof,HT800 Series

General specifications



Photo is representative

Product Name

Eaton HT800 pushbutton

Catalog Number

HT8FBRABFL7P

UPC

786685222806

Product Length/Depth

2.312 in

Product Height

3.25 in

Product Width

2 in

Product Weight

0.35 lb

Warranty

1 year

Compliances

CE Marked

Certifications

CSA Certified

UL Listed

defaultTaxonomyAttributeLabel

Special features

low profile light units

Type

30.5 mm, Watertight/Oiltight-HT800

Enclosure

NEMA 4X

NEMA 12

NEMA 3

NEMA 3R

NEMA 4

Operating mode

Pull: maintained

Push: maintained

Contact configuration

1 NO-1 NC

Illumination

Illuminated

Series

HT800

Options

Fingerproof

Light unit type

LED, full voltage

Light unit voltage

120 Vac/dc

Lens color

Red

Number of positions

2

Rating

NEMA 4

NEMA 13

NEMA 3R

NEMA 3

NEMA 12

NEMA 4X

Product category

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - HT8FBRABFL7P

Quick Selector - HT800 Pilot Devices

Illuminated push-pull units with low profile light units



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)