

Eaton HT8FBRBFL3

Catalog Number: HT8FBRBFL3

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units,low profile light units,Standard Actuator,Red,1NC,Illuminated,Red,LED, full voltage,24 Vac/Vdc Light Unit,Two-position,Maintained push, maintained pull,40 mm,HT800 Series

General specifications



Photo is representative

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8FBRBFL3
UPC	Product Length/Depth
786685222530	3 in
Product Height	Product Width
5 in	2 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Special features

low profile light units

Type

30.5 mm, Watertight/Oiltight-HT800

Enclosure

NEMA 12

NEMA 4

NEMA 3R

NEMA 3

NEMA 4X

Operating mode

Push: maintained

Pull: maintained

Contact configuration

1 NC

Illumination

Illuminated

Series

HT800

Light unit type

LED, full voltage

Light unit voltage

24 Vac/dc

Lens color

Red

Number of positions

2

Rating

NEMA 12

NEMA 4

NEMA 4X

NEMA 3

NEMA 13

NEMA 3R

Product category

Illuminated push-pull units with low profile light units

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - HT8FBRBFL3

Quick Selector - HT800 Pilot Devices



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)