

Eaton HT8FBRD1BVL7

Catalog Number: HT8FBRD1BVL7

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units, low profile light units, Standard Actuator, Red, 1NO-1NCLB, Illuminated, Red, Incandescent, full voltage, 120 Vac/Vdc Light Unit, Two-position, Maintained push, maintained pull, HT800 Series

General specifications



Photo is representative

Product Name

Eaton HT800 pushbutton

UPC

786685222660

Product Height

3.25 in

Product Weight

0.35 lb

Compliances

CE Marked

Catalog Number

HT8FBRD1BVL7

Product Length/Depth

2.312 in

Product Width

2 in

Warranty

1 year

Certifications

UL Listed

CSA Certified



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

low profile light units

Type

30.5 mm, Watertight/Oiltight-HT800

Enclosure

NEMA 4X

NEMA 3

NEMA 12

NEMA 3R

NEMA 4

Operating mode

Pull: maintained

Push: maintained

Contact configuration

1 NO-1 NCLB

Illumination

Illuminated

Series

HT800

Light unit type

Incandescent, full voltage

Light unit voltage

120 Vac/dc

Lens color

Red

Number of positions

2

Rating

NEMA 12

NEMA 4X

NEMA 4

NEMA 3R

NEMA 3

NEMA 13

Product category

Illuminated push-pull units with low profile light units

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Quick Selector - HT800 Pilot Devices](#)

[Eaton Specification Sheet - HT8FBRD1BVL7](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)