

Eaton HT8FBRVL7

Catalog Number: HT8FBRVL7

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units, low profile light units, Standard Actuator, Red, Illuminated, Red, Incandescent, full voltage, 120 Vac/Vdc Light Unit, Two-position, Maintained push, maintained pull, HT800 Series

General specifications



Photo is representative

Product Name
Eaton HT800 pushbutton

UPC
786685222462

Product Height
5 in

Product Weight
0.4 lb

Compliances
CE Marked

Catalog Number
HT8FBRVL7

Product Length/Depth
3 in

Product Width
2 in

Warranty
1 year

Certifications
UL Listed
CSA Certified

defaultTaxonomyAttributeLabel

Special features

low profile light units

Type

30.5 mm, Watertight/Oiltight-HT800

Enclosure

NEMA 4

NEMA 12

NEMA 4X

NEMA 3

NEMA 3R

Operating mode

Pull: maintained

Push: maintained

Illumination

Illuminated

Series

HT800

Light unit type

Incandescent, full voltage

Light unit voltage

120 Vac/dc

Lens color

Red

Number of positions

2

Rating

NEMA 13

NEMA 3R

NEMA 4

NEMA 3

NEMA 12

NEMA 4X

Product category

Illuminated push-pull units with low profile light units

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Quick Selector - HT800 Pilot Devices

Eaton Specification Sheet - HT8FBRVL7



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)