

# Eaton HT8GBGABV3-POP

Catalog Number: HT8GBGABV3-POP

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight, Illuminated pushbutton, NEMA 3, 3R, 4, 4X, 12 and 13, Momentary, Extended, Incandescent, full voltage light unit, 1NO-1NC, Green lens, 24 Vac/dc, Chrome bezel

## General specifications



Photo is representative

### Product Name

Eaton HT800 pushbutton

### UPC

786685284934

### Product Height

3 in

### Product Weight

0.5 lb

### Certifications

UL Listed

CSA Certified

### Catalog Number

HT8GBGABV3-POP

### Product Length/Depth

7 in

### Product Width

6 in

### Warranty

1 year

## defaultTaxonomyAttributeLabel

### Application

Pushbutton

### Special features

HT800 series

### Type

30.5 mm, Watertight/Oiltight

### Actuator color

Green

### Bezel

Chrome

### Actuator function

Momentary

### Enclosure

NEMA 12

NEMA 3R

NEMA 13

NEMA 4X

NEMA 3

NEMA 4

### Actuator

Extended

### Operating mode

Momentary

### Contact configuration

1 NO-1 NC

### Illumination

Illuminated

### Light unit type

Incandescent, full voltage

### Light unit voltage

24 Vac/dc

### Lens color

Green

### Product category

Illuminated pushbuttons

## Resources

### Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Quick Selector - HT800 Pilot Devices

Eaton Specification Sheet - HT8GBGABV3-POP

Operator material

Plastic



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)