

Eaton HT8GBGABV7-POP

Catalog Number: HT8GBGABV7-POP

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight, Illuminated pushbutton, NEMA 3, 3R, 4, 4X, 12 and 13, Momentary, Extended, Incandescent, full voltage light unit, 1NO-1NC, Green lens, 120 Vac/dc, Chrome bezel

General specifications



Photo is representative

Product Name

Eaton HT800 pushbutton

UPC

786685284927

Product Height

3 in

Product Weight

0.5 lb

Certifications

UL Listed

CSA Certified

Catalog Number

HT8GBGABV7-POP

Product Length/Depth

7 in

Product Width

6 in

Warranty

1 year

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

HT800 series

Type

30.5 mm, Watertight/Oiltight

Actuator color

Green

Bezel

Chrome

Actuator function

Momentary

Enclosure

NEMA 3

NEMA 12

NEMA 3R

NEMA 13

NEMA 4X

NEMA 4

Actuator

Extended

Operating mode

Momentary

Contact configuration

1 NO-1 NC

Illumination

Illuminated

Light unit type

Incandescent, full voltage

Light unit voltage

120 Vac/dc

Lens color

Green

Product category

Illuminated pushbuttons

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Quick Selector - HT800 Pilot Devices

Eaton Specification Sheet - HT8GBGABV7-POP

Operator material

Plastic



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)