

Eaton HT8GDBABF7

Catalog Number: HT8GDBABF7

Eaton 30.5 mm Watertight/Oiltight Pushbutton, Extended Actuator, Chrome bezel, 1NO-1NC, Illuminated, Blue lens, LED, full voltage, 120 Vac/Vdc Light Unit, Momentary, Plastic, Guarded, HT800 Series



Photo is representative

General specifications

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8GDBABF7
UPC	Product Length/Depth
782116302994	6.55 in
Product Height	Product Width
1.4 in	2 in
Product Weight	Warranty
0.7 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Bezel

Chrome

Enclosure

NEMA 4X

NEMA 12

NEMA 4

NEMA 3R

NEMA 3

NEMA 13

Actuator

Extended

Operating mode

Momentary

Contact configuration

1 NO-1 NC

Illumination

Illuminated

Light unit type

LED, full voltage

Light unit voltage

120 Vac/dc

Lens color

Blue

Product category

Guarded illuminated pushbuttons

Operator material

Plastic

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - HT8GDBABF7](#)

[Quick Selector - HT800 Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)