

Eaton HT8GDBF3

Catalog Number: HT8GDBF3

30.5 mm, Watertight/Oiltight-HT800, Guarded illuminated pushbutton, NEMA 3, 3R, 4, 4X, 12 and 13, Momentary, Extended, LED, full voltage light unit, Blue lens, 24 Vac/dc, Chrome bezel, Plastic



Photo is representative

General specifications

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8GDBF3
UPC	Product Length/Depth
782116302437	2.4 in
Product Height	Product Width
3.2 in	2.1 in
Product Weight	Warranty
0.4 lb	1 year
Certifications	
CSA Certified	
UL Listed	

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Bezel

Chrome

Enclosure

NEMA 13

NEMA 4

NEMA 3R

NEMA 4X

NEMA 12

NEMA 3

Actuator

Extended

Operating mode

Momentary

Illumination

Illuminated

Light unit type

LED, full voltage

Light unit voltage

24 Vac/dc

Lens color

Blue

Product category

Guarded illuminated pushbuttons

Operator material

Plastic

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - HT8GDBF3

Quick Selector - HT800 Pilot Devices



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)