

Eaton HT8GDCBF7

Catalog Number: HT8GDCBF7

Eaton 30.5 mm Watertight/Oiltight Pushbutton, Extended Actuator, Chrome bezel, 1NC, Illuminated, Clear lens, LED, full voltage, 120 Vac/Vdc Light Unit, Momentary, Plastic, Guarded, HT800 Series

General specifications



Photo is representative

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8GDCBF7
UPC	Product Length/Depth
782116302895	6.55 in
Product Height	Product Width
1.4 in	2 in
Product Weight	Warranty
0.7 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Bezel

Chrome

Enclosure

NEMA 4X

NEMA 4

NEMA 13

NEMA 12

NEMA 3

NEMA 3R

Actuator

Extended

Operating mode

Momentary

Contact configuration

1 NC

Illumination

Illuminated

Light unit type

LED, full voltage

Light unit voltage

120 Vac/dc

Lens color

Clear

Product category

Guarded illuminated pushbuttons

Operator material

Plastic

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Quick Selector - HT800 Pilot Devices

Eaton Specification Sheet - HT8GDCBF7



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)