

Eaton HT8GDGABV7

Catalog Number: HT8GDGABV7

Eaton 30.5 mm Watertight/Oiltight Pushbutton, Extended, Green Actuator, Chrome bezel, 1NO-1NC, Illuminated, Green lens, Incandescent, full voltage, 120 Vac/Vdc Light Unit, Momentary, Plastic, Guarded, HT800 Series

General specifications



Photo is representative

| | |
|------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton HT800 pushbutton | HT8GDGABV7 |
| UPC | Product Length/Depth |
| 782116302246 | 6.55 in |
| Product Height | Product Width |
| 1.4 in | 2 in |
| Product Weight | Warranty |
| 0.7 lb | 1 year |
| Compliances | Certifications |
| CE Marked | UL Listed CSA Certified |

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Bezel

Chrome

Enclosure

NEMA 3R

NEMA 4X

NEMA 3

NEMA 12

NEMA 4

NEMA 13

Actuator

Extended

Operating mode

Momentary

Contact configuration

1 NO-1 NC

Illumination

Illuminated

Light unit type

Incandescent, full voltage

Light unit voltage

120 Vac/dc

Lens color

Green

Product category

Guarded illuminated pushbuttons

Operator material

Plastic

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - HT8GDGABV7](#)

[Quick Selector - HT800 Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)