

# Eaton HT8GDYBF3

Catalog Number: HT8GDYBF3

Eaton 30.5 mm Watertight/Oiltight Pushbutton, Extended Actuator, Chrome bezel, 1NC, Illuminated, Yellow lens, LED, full voltage, 24 Vac/Vdc Light Unit, Momentary, Plastic, Guarded, HT800 Series

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton HT800 pushbutton	HT8GDYBF3
<b>UPC</b>	<b>Product Length/Depth</b>
782116302567	6.55 in
<b>Product Height</b>	<b>Product Width</b>
1.4 in	2 in
<b>Product Weight</b>	<b>Warranty</b>
0.7 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
	CSA Certified

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Watertight/Oiltight-HT800

### Bezel

Chrome

### Enclosure

NEMA 3R

NEMA 13

NEMA 4X

NEMA 3

NEMA 4

NEMA 12

### Actuator

Extended

### Operating mode

Momentary

### Contact configuration

1 NC

### Illumination

Illuminated

### Light unit type

LED, full voltage

### Light unit voltage

24 Vac/dc

### Lens color

Yellow

### Product category

Guarded illuminated pushbuttons

### Operator material

Plastic

## Resources

### Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - HT8GDYBF3

Quick Selector - HT800 Pilot Devices



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)