

Eaton HT8GDYBV3

Catalog Number: HT8GDYBV3

Eaton 30.5 mm Watertight/Oiltight Pushbutton, Extended Actuator, Chrome bezel, 1NC, Illuminated, Yellow lens, Incandescent, full voltage, 24 Vac/Vdc Light Unit, Momentary, Plastic, Guarded, HT800 Series

General specifications



Photo is representative

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8GDYBV3
UPC	Product Length/Depth
782116301867	6.55 in
Product Height	Product Width
1.4 in	2 in
Product Weight	Warranty
0.7 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Bezel

Chrome

Enclosure

NEMA 12

NEMA 3R

NEMA 3

NEMA 4X

NEMA 13

NEMA 4

Actuator

Extended

Operating mode

Momentary

Contact configuration

1 NC

Illumination

Illuminated

Light unit type

Incandescent, full voltage

Light unit voltage

24 Vac/dc

Lens color

Yellow

Product category

Guarded illuminated pushbuttons

Operator material

Plastic

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Quick Selector - HT800 Pilot Devices

Eaton Specification Sheet - HT8GDYBV3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)