

Eaton HT8GDYF1Q1L1

Catalog Number: HT8GDYF1Q1L1

Eaton 30.5 mm Watertight/Oiltight Pushbutton, Extended Actuator, Chrome bezel, 2NO-2NC, Illuminated, Yellow lens, LED, transformer, 120 Vac Light Unit, Momentary, Plastic, Guarded, HT800 Series

General specifications



Photo is representative

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8GDYF1Q1L1
UPC	Product Length/Depth
782116301652	6.55 in
Product Height	Product Width
1.4 in	2 in
Product Weight	Warranty
0.7 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified

defaultTaxonomyAttributeLabel

Type

30.5 mm, Watertight/Oiltight-HT800

Bezel

Chrome

Enclosure

NEMA 4

NEMA 3R

NEMA 13

NEMA 4X

NEMA 3

NEMA 12

Actuator

Extended

Operating mode

Momentary

Contact configuration

2 NO-2 NC

Illumination

Illuminated

Light unit type

LED, transformer

Light unit voltage

120 Vac/dc

Lens color

Yellow

Product category

Guarded illuminated pushbuttons

Operator material

Plastic

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - HT8GDYF1Q1L1](#)

[Quick Selector - HT800 Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)