

# Eaton HT8GDYL1

Catalog Number: HT8GDYL1

Eaton 30.5 mm Watertight/Oiltight Pushbutton, Extended Actuator, Chrome bezel, Illuminated, Yellow lens, LED, transformer, 120 Vac Light Unit, Momentary, Plastic, Guarded, HT800 Series

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton HT800 pushbutton	HT8GDYL1
<b>UPC</b>	<b>Product Length/Depth</b>
782116301379	6.55 in
<b>Product Height</b>	<b>Product Width</b>
1.4 in	2 in
<b>Product Weight</b>	<b>Warranty</b>
0.7 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	UL Listed
	CSA Certified

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Watertight/Oiltight-HT800

### Bezel

Chrome

### Enclosure

NEMA 4

NEMA 3R

NEMA 13

NEMA 12

NEMA 4X

NEMA 3

### Actuator

Extended

### Operating mode

Momentary

### Illumination

Illuminated

### Light unit type

LED, transformer

### Light unit voltage

120 Vac/dc

### Lens color

Yellow

### Product category

Guarded illuminated pushbuttons

### Operator material

Plastic

## Resources

### Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Quick Selector - HT800 Pilot Devices](#)

[Eaton Specification Sheet - HT8GDYL1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)