

# Eaton HT8GVAV7

Catalog Number: HT8GVAV7

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight, Push-to-test light unit, NEMA 1, 2, 3, 3R, 4, 4X, 12, Illuminated, Push-to-test, Incandescent, full voltage light unit, Amber lens, Plastic, 120 Vac/dc, Chrome bezel\_



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton HT800 pushbutton	HT8GVAV7
<b>UPC</b>	<b>Product Length/Depth</b>
782113964676	3 in
<b>Product Height</b>	<b>Product Width</b>
5 in	2 in
<b>Product Weight</b>	<b>Warranty</b>
0.4 lb	1 year
<b>Certifications</b>	
UL Listed	
CSA Certified	

## defaultTaxonomyAttributeLabel

### Application

Pushbutton

### Special features

HT800 series

### Type

30.5 mm, Watertight/Oiltight

### Actuator color

Amber

### Bezel

Chrome

### Actuator function

Momentary

### Enclosure

NEMA 1

NEMA 12

NEMA 3R

NEMA 4X

NEMA 3

NEMA 4

NEMA 2

### Actuator

Push-to-test

### Illumination

Illuminated

### Style type

30.5 mm

### Light unit type

Incandescent, full voltage

### Light unit voltage

120 Vac/dc

### Lens color

Amber

### Lens type

Plastic

### Product category

Push-to-test light unit

## Resources

### Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - HT8GVAV7

Quick Selector - HT800 Pilot Devices



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)