

Eaton HT8GVV3

Catalog Number: HT8GVV3

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight, Push-to-test light unit, NEMA 1, 2, 3, 3R, 4, 4X, 12, Illuminated, Push-to-test, Incandescent, full voltage light unit, White lens, Plastic, 24 Vac/dc, Chrome bezel



Photo is representative

General specifications

Product Name	Catalog Number
Eaton HT800 pushbutton	HT8GVV3
UPC	Product Length/Depth
782113964751	4.25 in
Product Height	Product Width
1.4 in	2 in
Product Weight	Warranty
0.01 lb	1 year
Certifications	
UL Listed	
CSA Certified	

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

HT800 series

Type

30.5 mm, Watertight/Oiltight

Actuator color

White

Bezel

Chrome

Actuator function

Momentary

Enclosure

NEMA 12

NEMA 4X

NEMA 3R

NEMA 2

NEMA 1

NEMA 3

NEMA 4

Actuator

Push-to-test

Illumination

Illuminated

Light unit type

Incandescent, full voltage

Light unit voltage

24 Vac/dc

Lens color

White

Lens type

Plastic

Product category

Push-to-test light unit

Resources

Brochures

Pushbuttons and Indicating Lights

HT800 30.5 mm pilot devices

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Quick Selector - HT800 Pilot Devices

Eaton Specification Sheet - HT8GVVW3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)