

Eaton HT8LEDRF1

Catalog Number: HT8LEDRF1

30.5 mm, Watertight/Oiltight-HT800, Replacement LED Bulb, 30.5 mm, watertight/oiltight-HT800, Red, Red, Red, 6-12 Vac/Vdc, 30.5 mm, Replacement LED bulb, HT800, HT800 Series pushbuttons and indicating lights, 6-12V

General specifications



Photo is representative

Product Name	Catalog Number
Eaton HT800 pushbutton LED	HT8LEDRF1
UPC	Product Length/Depth
782113683072	1 in
Product Height	Product Width
0.5 in	0.5 in
Product Weight	Warranty
0.02 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

Catalog Notes

For use with transformers with 6V secondary winding

defaultTaxonomyAttributeLabel

Type

Pushbutton accessory

Used with

HT800 Series pushbuttons and indicating lights

Series

HT800

Color

Red

Lens color

Red

Light color

Red

Voltage rating

6-12 V

Light unit voltage

6-12 Vac/dc

Product category

Replacement LED bulb

Size

30.5 mm

Resources

Brochures

[Pushbuttons and Indicating Lights](#)

[HT800 30.5 mm pilot devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Quick Selector - HT800 Pilot Devices](#)

[Eaton Specification Sheet - HT8LEDRF1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia