

Eaton IG6362V

Catalog Number: IG6362V

Eaton Arrow Hart extra heavy-duty industrial specification grade decorator duplex receptacle,#14-10 AWG,20A,Industrial,Flush,125V,Back and side,Ivory,Brass,High-impact nylon face,Glass-filled nylon base,5-20R,Duplex,Screw,Core pack



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty industrial specification grade decorator duplex receptacle	IG6362V
	UPC
	032664720574
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.138 in	0.37 lb

Certifications

UL
NOM
Federal Specification Classification 6233
01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Decorator duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Isolated ground

Terminal guards

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

Glass-filled nylon

Packaging type

Core pack

Color

Ivory

Connection type

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Arrow Hart extra heavy-duty hospital grade isolated ground straight blade decorator receptacles spec sheet](#)

[Eaton Specification Sheet - IG6362V](#)

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Design type

Straight blade

Face/body material

Glass-filled nylon base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)