

# Eaton IG6362W

Catalog Number: IG6362W

Eaton Arrow Hart extra heavy-duty industrial specification grade decorator duplex receptacle,#14-10 AWG,20A,Industrial,Flush,125V,Back and side,White,Brass,High-impact nylon face,Glass-filled nylon base,5-20R,Duplex,Screw,Core pack



## General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty industrial specification grade decorator duplex receptacle	IG6362W UPC 032664720581
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.138 in	0.37 lb

## Certifications

UL  
NOM  
Federal Specification Classification 6233  
01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Decorator duplex receptacle

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Isolated ground

Terminal guards

### Application

Industrial

### Device grade

Extra heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

Glass-filled nylon

### Packaging type

Core pack

### Color

White

### Connection type

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - IG6362W](#)

[Arrow Hart extra heavy-duty hospital grade isolated ground straight blade decorator receptacles spec sheet](#)

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Glass-filled nylon base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)