

Eaton L1430CY

Catalog Number: L1430CY

Eaton severe duty locking connector, #18-10 AWG, 30A, Industrial, 125/250V, Back wiring, Yellow, black, Severe duty, L14-30, Three-pole, Four-wire, Santoprene thermoplastic elastomeric, 0.63 to 1.16 in



General specifications

Product Name	Catalog Number
Eaton Arrow Hart severe duty locking connector	L1430CY
	UPC
	040893643496
Product Length/Depth	Product Height
6.75 in	4 in
Product Width	Product Weight
4.25 in	0.66 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	NOM

defaultTaxonomyAttributeLabel

Special features

Watertight locking connector

Type

Locking connector

Amperage Rating

30A

Voltage rating

125/250 V

Contact material

Nickel plated brass

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back

Environmental conditions

Corrosion resistant

Number of wires

Grounding

4

Number Of Poles

Three-pole

Color

Yellow

Black

Cord diameter

0.63-1.16 in (15.9-29.4 mm)

Material

Santoprene thermoplastic elastomeric

Operating temperature

-40 to 75 °C (-40 to 167 °F)

Allowable wire size

#18-10 AWG

NEMA configuration

Resources

Brochures

[Complex environment devices brochure](#)

Specifications and datasheets

[Eaton Specification Sheet - L1430CY](#)

L14-30

Torque rating

20 lbf-inch

Design type

Safety grip

Face/body material

Nylon



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia