

Eaton LR25 CGN

Catalog Number: LR25 CGN

Eaton Crouse-Hinds series Condulet Series 5 conduit outlet body, Rigid/IMC, Copper-free aluminum, LR shape, Body, traditional cover and gasket, 3/4"

General specifications



Product Name

Eaton Crouse-Hinds series Condulet
Series 5 conduit outlet body

Catalog Number

LR25 CGN

UPC

784564744302

Product Length/Depth

5.07 in

Product Height

2.28 in

Product Width

1.64 in

Product Weight

0.48 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Shape

LR

Conduit type

Rigid/IMC

Trade size

3/4"

Material

Copper-free aluminum

Special features

Body, traditional cover and gasket

Resources

Brochures

[Crouse-Hinds series Series 5 brochure](#)

Catalogs

[Crouse-Hinds series Series 5 catalog page](#)

Certification reports

[Condulet Series 5 Conduit Outlet Bodies Canadian certification](#)

[Condulet Series 5 Conduit Outlet Bodies UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - LR25 CGN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)