

Eaton LS-11

Catalog Number: LS-11

Eaton LS-Titan Miniature DIN Limit Switch, Top Push Plunger, Polyamide PA66-GF25 enclosure, 6A max AC, 3A max DC, 1NO-1NC, Slow Make Before Break, Positive Opening, 6A at 240Vac, 3A at 24Vdc, Cage Clamp, $\pm 0.02\text{mm}$ accuracy

General specifications



Photo is representative

Product Name	Catalog Number
Eaton LS-Titan miniature DIN limit switch LS-11	
UPC	Product Length/Depth
786685514178	1.22 in
Product Height	Product Width
2.99 in	1.32 in
Product Weight	Warranty
0.1188 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Listed

Type

LS-Titan

Contact Rating

6A at 240Vac, 3A at 24Vdc

Accuracy

±0.02mm

Enclosure material

Polyamide PA66-GF25

Connection

Cage clamps

Contact configuration

1 NO-1 NC, slow make before break, positive opening

Switch type

Top push plunger

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Environmental rating

IP66, IP67

Maximum AC current

6 A

Maximum DC current

3 A

Specifications and datasheets[Eaton Specification Sheet - LS-11](#)