

# Eaton LS4-S11-1-I-ZB

Catalog Number: LS4-S11-1-I-ZB

Eaton Interlock Switch, LS-Titan, Cabinet door interlock, Screw Terminals, 6A at 230 Vac, 3A at 24 Vdc, Full-size DIN, 1NO-1NC with positive opening contact



## General specifications

Product Name	Catalog Number
Eaton LS-Titan miniature DIN limit switch	LS4-S11-1-I-ZB
UPC	Product Length/Depth
786685393896	4.92 in
Product Height	Product Width
1.57 in	1.57 in
Product Weight	Warranty
0.25 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Listed

## defaultTaxonomyAttributeLabel

### Type

LS-Titan

### Contact Rating

6A at 230 Vac, 3A at 24 Vdc

### Enclosure material

Plastic

### Connection

Screw terminal

### Contact configuration

1 NO-1 NC with positive opening contact

### Series

LS-Titan

### Switch type

Cabinet door interlock

### Operating temperature - max

158 °F

### Operating temperature - min

-13 °F

### Environmental rating

IP65

### Maximum AC current

6 A at 230 Vac

### Maximum DC current

3 A at 24 Vdc

### Mounting method

Full-size DIN rail

## Resources

### Brochures

[LS-Titan Safety Limit Switches](#)

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - LS4-S11-1-I-ZB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)