

Eaton LSR-S02-1-I-TS

Catalog Number: LSR-S02-1-I-TS

Eaton LS-Titan Safety Interlock Switch, Cabinet Door Hinge Switch, Polyamide PA66-GF25 enclosures, 6A max AC, 3A max DC, 2NC, Slow Make Break, Positive Opening, 6A at 230Vac, 0.5A at 250Vdc, Screw Terminals



General specifications

Product Name	Catalog Number
Eaton LS-Titan Key interlock safety switches	LSR-S02-1-I-TS
	UPC
	786685393872
Product Length/Depth	Product Height
1.18 in	3.5 in
Product Width	Product Weight
2.24 in	0.1875 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

LS-Titan

Contact Rating

6A at 230Vac, 0.5A at 250Vdc

Enclosure material

Polyamide PA66-GF25

Connection

Screw terminal

Contact configuration

2 NC, slow make break, positive opening

Switch type

Cabinet door hinge switch

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Environmental rating

IP66, IP67

Maximum AC current

6 A

Maximum DC current

3 A

Resources

Brochures

[LS-Titan Safety Limit Switches](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - LSR-S02-1-I-TS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)