

# Eaton LS-S02-ZB

Catalog Number: LS-S02-ZB

Eaton Safety Interlock Switch, LS-Titan, Cabinet door interlock, Screw Terminals, 6A at 230 Vac, 3A at 24 Vdc, Miniature DIN, 2NC with positive opening contacts



## General specifications

Product Name	Catalog Number
Eaton LS-Titan miniature DIN limit switch LS-S02-ZB	
UPC	Product Length/Depth
786685393865	3.78 in
Product Height	Product Width
1.18 in	1.18 in
Product Weight	Warranty
0.2 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Listed

## defaultTaxonomyAttributeLabel

### Type

LS-Titan

### Contact Rating

6A at 230 Vac, 3A at 24 Vdc

### Enclosure material

Plastic

### Connection

Screw terminal

### Contact configuration

2 NC with positive opening contacts

### Series

LS-Titan

### Switch type

Cabinet door interlock

### Operating temperature - max

158 °F

### Operating temperature - min

-13 °F

### Environmental rating

IP65

### Maximum AC current

6 A at 230 Vac

### Maximum DC current

3 A at 24 Vdc

### Mounting method

Miniature DIN rail

## Resources

### Brochures

[LS-Titan Safety Limit Switches](#)

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - LS-S02-ZB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)