

Eaton LTCOND100NMBL100

Catalog Number: LTCOND100NMBL100

Eaton Crouse-Hinds series liquidtight conduit, 100 ft, Black, 1.041-1.066" I.D., 1.290-1.315" O.D., PVC, 105°C dry, 60°C wet, 1" trade size, Type B

General specifications



Product Name

Eaton Crouse-Hinds series liquidtight conduit

Catalog Number

LTCOND100NMBL100

UPC

662277031950

Product Weight

27.75 lb

Photo is representative



Powering Business Worldwide

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Temperature rating

105°C dry, 60°C wet

Color

Black

Trade size

1"

Coil/reel size

100 ft

Inner diameter

1.041-1.066"

Outer diameter

1.290-1.315"

Type

B

Material

PVC

Resources

Catalogs

[Crouse-Hinds series Liquidtight Conduit catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - LTCOND100NMBL100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)