

Eaton LTCOND150NM50

Catalog Number: LTCOND150NM50

Eaton Crouse-Hinds series liquidtight conduit, 50 ft, Gray, 1.575-1.600" I.D., 1.865-1.900" O.D., PVC, 80°C dry, 60°C wet, 1-1/2" trade size, Type B

General specifications

Product Name

Eaton Crouse-Hinds series liquidtight conduit

Catalog Number

LTCOND150NM50

UPC

662277031868

Product Weight

24 lb



Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Temperature rating

80°C dry, 60°C wet

Color

Gray

Trade size

1-1/2"

Coil/reel size

50 ft

Inner diameter

1.575-1.600"

Outer diameter

1.865-1.900"

Type

B

Material

PVC

Resources

Catalogs

[Crouse-Hinds series Liquidtight Conduit catalog page](#)

Specifications and datasheets

[Eaton Specification Sheet - LTCOND150NM50](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)