

Eaton LY44M25T30CU

Catalog Number: LY44M25T30CU

Eaton Marine duty encapsulated transformer, marine duty encapsulated transformer, EPTM, copper, 243, 60 Hz, three-phase, 440 V, 220 V, 2 at +2.5% FCAN 4 at -2.5% FCBN, 115 °C rise, 30 KVA, indoor-outdoor, 85I30



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Marine duty encapsulated transformer	LY44M25T30CU
	UPC
	786680111358
Product Length/Depth	Product Height
10.52 in	17.38 in
Product Width	Product Weight
20 in	597 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

EPTM

Frame

243

Tap size

2 at +2.5% FCAN 4 at -2.5% FCBN

Type

Marine Duty Encapsulated Transformer

Wiring connection

85I30

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

440 V

Secondary Voltage

220 V

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - LY44M25T30CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)