

# Eaton M22-CLEDC-G

Catalog Number: M22-CLEDC-G

Eaton M22 modular pushbutton, LED Light Unit, Base, Spring-cage, IP66, Illuminated, Green, 13-30 Vac/dc

Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton M22 modular pushbutton	M22-CLEDC-G
<b>UPC</b>	<b>Product Length/Depth</b>
786685277905	5 in
<b>Product Height</b>	<b>Product Width</b>
0.5 in	3 in
<b>Product Weight</b>	<b>Warranty</b>
0.03 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
GoST-R	CCC Marked
CE Marked	CSA Certified
Bureau Veritas	Lloyd's Register Certified



## Type

Light Unit

## Environmental rating

IP66

## Voltage rating

13-30 Vac/dc

## Illumination

Illuminated

## Series

M22

## Size

22.5 mm

## Actuator

Base, spring-cage

## Light color

Green

## Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

## Installation instructions

[M22 Operators and Accessories](#)

## Specifications and datasheets

[Global Data Sheet - M22-CLEDC-G](#)[Eaton Specification Sheet - M22-CLEDC-G](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)