

Eaton M22-CLEDC-W

Catalog Number: M22-CLEDC-W

Eaton M22 modular pushbutton, LED, Light Unit, Base, Spring-cage, IP66, Illuminated, White, 13-30 Vac/dc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-CLEDC-W
UPC	Product Length/Depth
786685277882	3 in
Product Height	Product Width
2 in	2 in
Product Weight	Warranty
0.1 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CSA Certified
Bureau Veritas	CCC Marked
GoST-R	Lloyd's Register Certified

Type

Light Unit

Environmental rating

IP66

Voltage rating

13-30 Vac/dc

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Base, spring-cage

Light color

White

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-CLEDC-W](#)

[Global Data Sheet - M22-CLEDC-W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)