

Eaton M22-D-G

Catalog Number: M22-D-G

Eaton 22.5 mm RMQ-Titan Pushbutton,Green Actuator,Silver bezel,IP67, IP69K,Non-illuminated,Flush mounting,NEMA 4X, 13,5,000,000 operations,Momentary,22.5 mm,Flush Pushbutton,M22

General specifications



Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-D-G
UPC	Product Length/Depth
786685275956	2 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.01 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
Bureau Veritas	CSA Certified
GoST-R	CCC Marked
CE Marked	Lloyd's Register Certified
Catalog Notes	
Includes contact block mounting adapter.	

defaultTaxonomyAttributeLabel

Type

Pushbutton

Actuator color

Green

Bezel

Silver

Actuator function

Momentary

Enclosure

IP67

IP69K

Button color

Green

Actuator

Flush, button

Operating mode

Momentary

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Operating cycles

5 million

Mounting method

Flush

Degree of protection

NEMA 4X

NEMA 13

Product category

Flush pushbutton

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-D-G](#)

[Eaton Specification Sheet - M22-D-G](#)

[Quick Selector - M22 Pushbuttons](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia