

Eaton M22-DG-B

Catalog Number: M22-DG-B

Eaton 22.5 mm RMQ-Titan Pushbutton, Guarded, Blue Actuator, Silver bezel, IP67, IP69K, Non-illuminated, Flush mounting, NEMA 4X, 13,5,000,000 operations, Momentary, 22.5 mm, Flush Pushbutton, M22

Photo is representative



General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-DG-B
UPC	Product Length/Depth
786685275253	7 in
Product Height	Product Width
1.5 in	5 in
Product Weight	Warranty
1 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
GoST-R	CSA Certified
CE Marked	CCC Marked
Bureau Veritas	Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

defaultTaxonomyAttributeLabel

Type

Pushbutton

Actuator color

Blue

Bezel

Silver

Actuator function

Momentary

Enclosure

IP69K

IP67

Button color

Blue

Actuator

Guarded

Operating mode

Momentary

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Operating cycles

5 million

Mounting method

Flush

Degree of protection

NEMA 4X

NEMA 13

Product category

Flush pushbutton

Size

22.5 mm

Resources

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Global Data Sheet - M22-DG-B

Eaton Specification Sheet - M22-DG-B

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)