

Eaton M22-D-G-GB1

Catalog Number: M22-D-G-GB1

Eaton 22.5 mm RMQ-Titan Pushbutton, START, Green Actuator, Silver bezel, IP67, IP69K, Non-illuminated, Flush mounting, NEMA 4X, 13,5,000,000 operations, Momentary, 22.5 mm, Flush Pushbutton, M22



General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-D-G-GB1
UPC	Product Length/Depth
786685276380	1 in
Product Height	Product Width
4 in	3 in
Product Weight	Warranty
1 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
GoST-R	CSA Certified
Bureau Veritas	CCC Marked
CE Marked	Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

defaultTaxonomyAttributeLabel

Type

Pushbutton

Actuator color

Green

Bezel

Silver

Actuator function

Momentary

Enclosure

IP69K

IP67

Button color

Green

Actuator

Flush, button

Operating mode

Momentary

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Etching code

START

Operating cycles

5 million

Mounting method

Flush

Degree of protection

NEMA 4X

NEMA 13

Inscription

START

Product category

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-D-G-GB1](#)

[Eaton Specification Sheet - M22-D-G-GB1](#)

Flush pushbutton

Size

22.5 mm



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)