

Eaton M22-DGH-R-X0

Catalog Number: M22-DGH-R-X0

Eaton 22.5 mm Modular Pushbutton Operator, RQM-Titan, Extended, Red Actuator, Silver bezel, X0 etching code, Non-illuminated, O, 5,000,000 operations, Momentary, Guarded, M22 Series



General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-DGH-R-X0
UPC	Product Length/Depth
786685275246	7 in
Product Height	Product Width
1.5 in	5 in
Product Weight	Warranty
0.03 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CSA Certified
GoST-R	CCC Marked
Bureau Veritas	Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

defaultTaxonomyAttributeLabel

Type

Pushbutton

Bezel

Silver guarded

Actuator function

Momentary

Button color

Red

Actuator

Extended with guard, button

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Etching code

X0

Operating cycles

5 million

Inscription

O

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[M22-DGH 2D PDF](#)

[M22-DGH AutoCAD 2D Footprint \(mm\)](#)

[M22-DGH AutoCAD 2D Footprint](#)

[M22-DGH 2D Drawing Xchange](#)

[M22-DGH 3D Model Xchange](#)

[M22-DGH 3D Inventor](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-DGH-R-X0](#)

[Global Data Sheet - M22-DGH-R-X0](#)