

Eaton M22-DLH-R-K12-R

Catalog Number: M22-DLH-R-K12-R

Eaton M22 modular pushbutton, Complete Device, 22.5 mm, Extended, Momentary, Illuminated, Bezel: Silver, Button: Red, 1NO-2NC, IP67, IP69K, NEMA 4X, 13, 12-30 Vac/dc

Photo is representative



General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-DLH-R-K12-R

UPC

786685556642

Product Length/Depth

1.46 in

Product Height

3.45 in

Product Width

1.18 in

Product Weight

0.085 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked
Bureau Veritas
GoST-R

Certifications

CCC Marked
CSA Certified
Lloyd's Register Certified

Catalog Notes

Positively driven contact blocks.

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

M22 series

Type

22.5 mm Modular

Bezel

Silver

Actuator function

Momentary

Button color

Red

Actuator

Button, extended

Contact configuration

1 NO-2 NC

Illumination

Illuminated

Series

M22

Voltage rating

12-30 Vac/dc

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Size

22.5 mm

Resources

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Global Data Sheet - M22-DLH-R-K12-R

Eaton Specification Sheet - M22-DLH-R-K12-R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)