

Eaton M22-D-X-SRG

Catalog Number: M22-D-X-SRG

Eaton 22.5 mm RMQ-Titan Pushbutton, Black, Red, Green Actuator, Silver bezel, IP67, IP69K, Non-illuminated, Flush mounting, NEMA 4X, 13,5,000,000 operations, Momentary, 22.5 mm, Flush Pushbutton, M22



General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-D-X-SRG
UPC	Product Length/Depth
786685276427	7 in
Product Height	Product Width
1.5 in	5 in
Product Weight	Warranty
1 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked GoST-R Bureau Veritas	CCC Marked CSA Certified Lloyd's Register Certified
Catalog Notes	
Includes contact block mounting adapter. Buttonless operator, comes with three color buttons.	

defaultTaxonomyAttributeLabel

Type

Pushbutton

Actuator color

Black, green, red

Bezel

Silver

Actuator function

Momentary

Enclosure

IP67

IP69K

Button color

Black, red, green

Actuator

Flush, button

Operating mode

Momentary

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Operating cycles

5 million

Mounting method

Flush

Degree of protection

NEMA 13

NEMA 4X

Product category

Flush pushbutton

Size

22.5 mm

Resources

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Eaton Specification Sheet - M22-D-X-SRG

Global Data Sheet - M22-D-X-SRG



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)