

Eaton M22-LED230-G-B20

Catalog Number: M22-LED230-G-B20

Eaton M22 pushbutton led, Modular Pushbutton, M22, 22.5 mm, Silver, Flush momentary, Green, Screw, Green, 85-264 Vac, NEMA 4x, 13, IP67, IP69K (IP66 key-release)

General specifications



Photo is representative

Product Name

Eaton M22 pushbutton led

Catalog Number

M22-LED230-G-B20

UPC

786680127649

Product Length/Depth

0.01 in

Product Height

0.01 in

Product Width

0.01 in

Product Weight

0.01 lb

Compliances

CE Marked

Certifications

CSA Certified

defaultTaxonomyAttributeLabel

Bezel

Silver

Enclosure

NEMA 13

NEMA 4X

Button color

Green

Operating mode

Flush momentary

Series

M22

Light color

Green

Environmental rating

IP67, IP69K (IP66 key-release)

Light unit voltage

85-264 Vac

Size

22.5 mm

Terminals

Screw

Resources

Brochures

[M22 Pilot Devices](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-LED230-G-B20](#)

[Eaton Specification Sheet - M22-LED230-G-B20](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)